



Rohrbürsten mit einfacher Spirale aus glattem, gehärtetem Stahl mit Kern aus Stahldraht oder weißem, glattem Nylon und gekräuseltem, vermessingtem Stahl, weniger aggressiv.

#### ART DER NUTZUNG

Reinigung von Rohrrinnenseiten. Die Rohrbürsten aus Nylon sind für die Reinigung von Rohren aus Edelstahl geeignet.

sitbrush.com

MM		INCH	
<b>A</b> mm	95	<b>A</b> inch	3-3/4
<b>D</b> mm	65	<b>D</b> inch	2-5/8
<b>L</b> mm	160	<b>L</b> inch	6-5/16
<b>Anschluss</b>	M12	<b>Anschluss</b>	M12
<b>CO/IS</b> pach	12	<b>CO/IS</b> pack	12
<b>Art.</b>	SC 65	<b>Art.</b>	SC 65
<b>Gewinde</b>	Vermessingter Stahl	<b>Gewinde</b>	Vermessingter Stahl
<b>Ø Gewinde</b>	0,30mm	<b>Ø Gewinde</b>	0,012"

Le dimensioni, le illustrazioni, le caratteristiche tecniche, le referenze e tutti gli altri dati contenuti nel catalogo possono essere modificati da SIT senza preavviso. Tutte le dimensioni riportate sul catalogo sono da considerarsi nominali e, se non diversamente specificato, sono in mm. Diametri, sporgenze e spessori degli insiemi di filamenti, costituenti le spazzole, sono da considerare tali solo approssimativamente.  
The dimensions, illustrations, technical characteristics and all other data contained in the catalogue may be changed by SIT without prior notice. All dimensions on the catalogue, unless otherwise specified, are in mm. Diameters, protrusions and thicknesses of sets of filaments forming the brushes are only approximate.